

Compression Terminal

By Burndy
Catalog # [YAL252N](#)



Copper HYLUGTM , 2 Hole w/ Inspection Window, 1/0 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing,12 index,Pink, Short Barrel, Tin Plated.

Application

Wire Termination

General

Color Code	Pink
Connector Type	STANDARD BARREL
Die Index	12
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810416914

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.72 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.84 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.63 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSD.029077-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAL252N-SPEC-EN | REV 6/2024