

Compression Terminal

By Burndy
Catalog # [YAL4CT10](#)

Copper HYLUG™, Single Hole w/ Inspection Window, 4 AWG, #10 Stud, 8 index, Grey, Short Barrel, Electro- Tin Plated.



Application

Wire Termination

General

Catalog Number	YAL4CT10
Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417515

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - D inch	0.47 in
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.51 in
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSD029213](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAL4CT10-SPEC-EN | REV 6/2024