



# Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog Number [YAV10T345BOX](#)



SEAMLESS UNINSULATED COMPRESSION HEAVY DUTY RING TONGUE TERMINAL.

## General

Connector Type	Ring Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810514030
UPC 12 Digit	7818105140300

## Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.58 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - N inch	0.23 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.48 in
Dimension - Stud Size inch	1/4
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Pallet Quantity	99999

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Technical Solutions - BURNDY\\_YAV10T345BOX\\_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YAV10T345BOX-SPEC-EN | REV 11/2023