



Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog Number [YAV14H34F](#)



Uninsulated Compression Terminal Fork Tongue With Shroud Seamless , 20 - 14 AWG, #8 -10, .96 in L, Tin Plated.

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810025031

Dimensions

Dimension - B Length fraction	2/7 in
Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.17 in
Dimension - Pad Width inch	0.37 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.23 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Navy Size	2 1/2 (1);2 1/2 (19);2 1/2 (26);3 (7);4 (1);4 (7);4 (19);4 (41)
Conductor - Copper Str Navy Size Range	2 1/2 (1)-4 (41)
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Sales Drawings - 50094188](#)
[Technical Solutions - BURNDY_YAV14H34F_Specsheet](#)



A proud member of the Hubbell Family.

