



# Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [YAV14L36](#)



Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Hole, 20-14 AWG(Str) / 20-12 AWG(Sol), #8-#10 Stud, Short Barrel, Tin Plated.

## Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

## General

|                                      |   |
|--------------------------------------|---|
| Catalog Number                       | YAV14L36  |
| Connector Type                       | Ring Terminal   |
| EU RoHS Indicator                    | Yes   |
| Feature - Barrel Style               | Chamfered   |
| Feature - Barrel Type                | Standard  |
| Material                             | Copper  |
| Material Composition                 | <ul style="list-style-type: none"> <li>• DLP Copper</li> <li>• Tin Plating</li> </ul> |
| Physical Attribute - Number of Holes | 1   |
| Physical Attribute - Tongue Type     | Ring  |
| Plated                               | Y   |
| Plating Type                         | Tin - Electro Plated  |
| Sub Brand                            | HYLUG   |
| Trade Name                           | HYLUG™  |
| Type                                 | Ring Tongue   |
| UPC                                  | 781810025185  |
| UPC 12 Digit                         | 7818100251855   |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Bolt Size fraction  | #8      |
| Dimension - D inch              | 0.30 in |
| Dimension - Hole Size fraction  | 1/5     |
| Dimension - Hole Size inch      | 0.19 in |
| Dimension - Hole Size mm        | 5 mm    |
| Dimension - Length Overall inch | 0.70 in |
| Dimension - N inch              | 0.16 in |
| Dimension - Pad Width inch      | 0.29 in |
| Dimension - Stud Size inch      | #8      |
| Dimension - Z (inch)            | 0.18 in |

## Conductor Related

|                                     |  |
|-------------------------------------|--|
| Conductor - Copper Solid Size       | 20 ;18 AWG;17 AWG;16 AWG;15 AWG;14 AWG;13 AWG;12 AWG   |
| Conductor - Copper Solid Size Range | 20 -12 AWG   |
| Conductor - Copper Str Size         | 20 AWG;18 AWG;16 AWG;14 AWG  |
| Conductor - Copper Str Size Range   | 20 AWG - 14 AWG  |
| Conductor Size                      | 16 - 14 AWG  |
| Conductor Type                      | <ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul> |

## Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | Yes   |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| UL Listed                          | Yes   |

## Logistics

|                 |       |
|-----------------|-------|
| Carton Quantity | 1000  |
| Pallet Quantity | 99999 |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Product Cross Section Image\(s\) - BUR\\_YAV10L36BOX\\_LineArt](#)  
[Sales Drawings - 50094160](#)



A proud member of the Hubbell Family.

