



Uninsulated Right Angle Ring Terminal For 16 - 14 AWG

By Burndy
Catalog Number [YAV14R](#)



Copper Right Angle Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN 20-14, #8-#10 Stud, Short Barrel, Electro-Tin Plated.

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025222

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - G inch	0.56 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	9 mm
Dimension - Length Overall inch	0.36 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	1/4
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z inch	0.25 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Size	20;18;16;14
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Sales Drawings - 50094165](#)
[Technical Solutions - BURNDY_YAV14R_Specsheet](#)



A proud member of the Hubbell Family.