

# Compression Terminal

By Burndy  
Catalog # [YAV252M12](#)

Hylug Copper tubing Compression terminals, 25 mm<sup>2</sup>, M12 Stud, 2 Holes, Tin Plated.



## Application

Metric Wire Termination

## General

Catalog Number	YAV252M12
Connector Type	METRIC
Die Index	9
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637807
UPC 12 Digit	7818106378077

## Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.2 mm
Dimension - L Length Overall mm	92.5 mm
Dimension - Length Overall inch	3.64 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Material	COPPER
Conductor Size	25 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

[3D Models - YAV252M12\\_MODEL-IGES](#)  
[3D Models - YAV252M12\\_MODEL-PDF](#)  
[3D Models - YAV252M12\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)  
[Sales Drawings - 50025887](#)