



Uninsulated Ring Terminal For 1/0 AWG (Nickel Plated)

By Burndy
Catalog # [YAV25L2NK](#)

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Window, AN-1/0 Flex, 5/16" Stud, Short Barrel, Nickel Plated.



General

Connector Type	Ring Terminal
Die Index	43
Feature - Barrel Style	<ul style="list-style-type: none">ChamferedSkived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810163139

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.85 in
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	2.03 in
Dimension - N inch	0.42 in
Dimension - Outside Diameter inch	0.57 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	5/16 in
Dimension - Z (inch)	0.43 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Aircraft Size	AN 0
Conductor Size	1/0 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Pallet Quantity	39200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094161_E](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV25L2NK-SPEC-EN | REV 6/2024

