



Uninsulated Ring Terminal For 2/0 AWG

By Burndy
Catalog # [YAV26L12BOX](#)

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Hole, AN 2/0 Flex, 5/8" Stud, Short Barrel, Tin Plated.



General

Catalog Number	YAV26L12BOX
Connector Type	Ring Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none">DLP CopperTin Plating

Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810540404

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	1.15 in
Dimension - Hole Size mm	17 mm
Dimension - Length Overall inch	2.52 in
Dimension - N inch	0.53 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size inch	5/8 in
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 00
Conductor - Copper Str Aircraft Size Range	AN 00
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YAV-L-BOX_LineArt](#)
[Sales Drawings - 50094161_E](#)



A proud member of the Hubbell Family.

