



Compression Terminal

By Burndy
Catalog # [YAV26L2NK](#)

Cu Tubing Hylug, 1 Hole with Inspection Window, AN-2/O Aircraft, 600V-35kV, 5/16" stud, Seamless, Compression.



Application

Wire Termination

General

Connector Type	STANDARD BARREL
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Nickel Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Nickel
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810139714
UPC 12 Digit	7818101397144

Dimensions

Dimension - B Length inch	0.782 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - Length Overall inch	2.319 in
Dimension - N inch	0.467 in
Dimension - Pad Width inch	0.934 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.48 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Aircraft Size	00 Aircraft
Conductor - Copper Str Size	2/O AWG
Conductor - Material	COPPER
Conductor Size	2/O AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	23200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094161_E](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV26L2NK-SPEC-EN | REV 6/2024

