



Compression Terminal

By Burndy
Catalog # [YAV26L2TC38FX45](#)

HYLUG™, Copper Compression Lug, 2 Holes, W/Insp Window, 2/0 Weld, (325/#24) DLO (Flex), 2/0 AWG (Code), 125 Navy, 600 V - 35 kV, 45 Deg Bent, Black, 13 Index.



Application

Wire Termination

General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
Feature - Barrel Style	- Chamfered - Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022320
UPC 12 Digit	7818100223200

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Height inch	1.38 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.05 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	3/8

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Navy Size Range	125 Navy
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 WELD
Conductor - CopperWeld Str Size Range	2/0 WELD
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Dimension - Z (inch)	0.43 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	11600

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SE..208119-01](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.