

Uninsulated Ring Terminal For 2/0 AWG

By Burndy
Catalog # [YAV26L31](#)

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Window, AN- 2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated.



General

Connector Type	Ring Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating

Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810088975

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.10 in
Dimension - N inch	0.39 in
Dimension - Pad Width inch	0.93 in
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.34 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN-2/0
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	29600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094161_E](#)