



Uninsulated Ring Terminal For 8 AWG (Nickel Plated)

By Burndy
Catalog Number [YAV8CLINK](#)

LARGE SIZE UNINSULATED COMPRESSION TERMINALS
SEAMLESS UNINSULATED COMPRESSION RING TONGUE
TERMINAL.



General

Connector Type	Ring Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810085684
UPC 12 Digit	7818100856844

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.58 in
Dimension - Length Overall inch	1.19 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200
Pallet Quantity	99999

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094161_E](#)
[Technical Solutions - BURNDY_YAV8CLINK_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV8CLINK-SPEC-EN | REV 11/2023