



Uninsulated Right Angle Ring Terminal For 8 AWG

By Burndy
Catalog Number [YAV8CRS3](#)



Copper Compression Right Angled Lug, Heavy Duty, 1 Hole W/ Inspection Hole, AN-8 Flex, 3/8" Stud, Short Barrel, Tin Plated.

General

Connector Type	Ring Terminal
Die Index	38
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810082188

Dimensions

Dimension - B Length fraction	4/9 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Size fraction	3/8
Dimension - G inch	0.84 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Pad Width inch	0.56 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.34 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Pallet Quantity	99999

Product Assets

[Sales Drawings - 50094166](#)
[Technical Solutions - BURNDY_YAV8CRS3_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV8CRS3-SPEC-EN | REV 11/2023