



# Uninsulated Ring Terminal For 10 - 9 AWG

By Burndy  
Catalog # [YAV9CT4BOX](#)



Uninsulated Cu Compression Terminal, Ring Tongue, #10 - #9 AWG, 5/16" stud.

## General

Catalog Number	YAV9CT4BOX
Connector Type	Ring Terminal
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810532201

## Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.39 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.34 in
Dimension - Hole Size fraction	32/97
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.23 in
Dimension - N inch	0.27 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Pad Width inch	0.52 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	5/16"
Dimension - Z (inch)	0.36 in

## Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG
Conductor - Copper Str Size Range	10 AWG - 9 AWG
Conductor Size	10 - 9 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YAV10T3BOX\\_LineArt](#)  
[Sales Drawings - 50094160](#)



A proud member of the Hubbell Family.