



Uninsulated Flag-Type Ring Terminal For 1 AWG

By Burndy
Catalog # [YBM1CL1](#)



Flag Type, Ring Tongue Electrolytic Cu Terminal, #1 AWG, 1/4" stud, 572 Index.

General

Connector Type	Flag Ring Terminal
Die Index	572
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080719

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.59 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.40 in
Dimension - N inch	0.3 in
Dimension - Outside Diameter inch	0.58 in
Dimension - Pad Width inch	0.66 in
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Size Range	1
Conductor - Copper Str Size Range	1
Conductor Size	1 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	57600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094169](#)



A proud member of the Hubbell Family.