



Uninsulated Flag-Type Ring Terminal For 4 AWG

By Burndy
Catalog # [YBM4CL4](#)

One Piece Extruded Hylugs Copper Terminal, Ring Tongue, #4 AWG Flex Class I, 4(105/#24) DLO, #4 AWG Code, #8 - #10 stud, 56 Index.



General

Catalog Number	YBM4CL4
Connector Type	Flag Ring Terminal
Die Index	56
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026267

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.27 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	4 (105/#24)
Conductor - Copper Flex I Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4 AWG
Conductor Size	4 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	800
Pallet Quantity	76800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094169](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YBM4CL4-SPEC-EN | REV 6/2024