

Compression C-Tap

By Burndy
Catalog # YC26L12TN

Cu Thin Wall C-Tap, Compression, 2/0 - #1 AWG(Main), #1 - #12 AWG(Tap), 600 V, Tin Plated.



Application

Wire Tap

General

Color Code	Purple
Connector Type	C-TAP
Die Index	15
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040256
UPC 12 Digit	7818100402566

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - D inch	1.75 in
Dimension - Pad Width inch	0.43 in
Dimension - Strip Length inch	1-13/16

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	2/0 AWG-1 AWG
Conductor - Copper Str Run Range	2/0 AWG-1 AWG
Conductor - Copper Str Tap	1 AWG-12 AWG
Conductor - Copper Str Tap Range	1 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	150
Minimum Pack Quantity	1
Pallet Quantity	27000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..208529-01](#)