


# YC2C4, Copper C-Shape Connector

By Burndy  
Catalog # YC2C4



CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 2 Sol. - 2 Str., Tap: 8 Sol. - 4 Str.

## Application

For Range Of Copper And Making Tap Or Parallel Copper Connections

## General

Catalog Number	YC2C4
Die Index	C
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810112250
UPC 12 Digit	7818101122500

## Dimensions

Dimension - Height inch	0.98 in
Dimension - L Length Overall mm	17 mm
Dimension - Length Overall inch	0.67 in

## Conductor Related

Conductor - Copper Solid Run	4 AWG;2 AWG
Conductor - Copper Solid Run Range	4 AWG-2 AWG
Conductor - Copper Solid Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Tap Range	8 AWG-4 AWG
Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	4 Sol. - 2 Str
Conductor - Copper Str Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Tap Range	8 Sol. - 4 Str
Conductor Type	Cu C Sol-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - Industry Standards Met	UL 486A;UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Pallet Quantity	23200

## Product Assets

[3D Models - YC2C4\\_MODEL-IGES](#)  
[3D Models - YC2C4\\_MODEL-PDF](#)  
[3D Models - YC2C4\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YCC\\_Lineart](#)  
[Sales Drawings - SE..090670-01](#)

