

Compression C-Tap

By Burndy
Catalog # [YC3L12TN](#)

Cu Thin Wall C-Tap, Compression, #3 - #5 AWG(Main), #5 - #12 AWG(Tap), 600 V, Tin Plated.



Application

Wire Tap

General

Color Code	Green
Connector Type	C-TAP
Die Index	11
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040218
UPC 12 Digit	7818100402188

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.46 in
Dimension - D inch	1.18 in
Dimension - Pad Width inch	0.27 in
Dimension - Strip Length inch	1-3/16

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	3 AWG-5 AWG
Conductor - Copper Str Run Range	3 AWG-5 AWG
Conductor - Copper Str Tap	5 AWG-12 AWG
Conductor - Copper Str Tap Range	5 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	3 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Pallet Quantity	46400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..208529-01](#)