



## Compression C-Tap

By Burndy  
Catalog # [YC4L12TN](#)

Cu Thin Wall C-Tap, Compression, #4 - #6 AWG(Main), #6 - #12 AWG(Tap), 600 V, Tin Plated.



### Application

Wire Tap

### General

Color Code	Pink
Connector Type	C-TAP
Die Index	10
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040201
UPC 12 Digit	7818100402011

### Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.39 in
Dimension - D inch	1.18 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	1-3/16

### Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

### Conductor Related

Conductor - Copper Str Run	4 AWG-6 AWG
Conductor - Copper Str Run Range	4 AWG-6 AWG
Conductor - Copper Str Tap	6 AWG-12 AWG
Conductor - Copper Str Tap Range	6 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG-12 AWG
Conductor Type	CODE

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	500
Pallet Quantity	74000

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SC..208529-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YC4L12TN-SPEC-EN | REV 6/2024