

YCA252NTN, Copper compression terminal, 2-holes, No Skive, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy

Catalog # [YCA252NTN](#)

Cu Compression terminal, 2 holes W/O/insp Window, 1/0 AWG, 1/2"stud, 5.34"L.

General

Catalog Number	YCA252NTN
Connector Type	Terminal
Die Index	165
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810055861
UPC 14 Digit GTIN	00781810055861

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.62 in



Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-5/8 in
Dimension - Z (inch)	2.37 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	1/0
-----------------------------	-----

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Pallet Quantity	7400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..029071-01](#)
[Specifications - YCA252NTN Specification Sheet English](#)
[Specifications - YCA252NTN Specification Sheet French](#)