



YCA272NTN, Copper compression terminal, 2-Hole, 3/0 Str, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA272NTN](#)



Cu Compression terminal, 3/0 str, .56"stud,5.33"L.

General

Catalog Number	YCA272NTN
Connector Type	Terminal
Die Index	167;207;211
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810216033

Dimensions

Dimension - B Length fraction	1-20/29 in
Dimension - B Length inch	1.69 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	135 mm
Dimension - Length Overall inch	5.33 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.79 in
Dimension - Pad Width inch	1.08 in
Dimension - Strip Length inch	1 3/4
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	3/0 AWG
-----------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Pallet Quantity	4608

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd029071-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YCA272NTN-SPEC-EN | REV 6/2024