

YCA2C2N, Copper compression terminal, 2-hole pad, #2 AWG Str, 1/2" Stud, 1-3/4" Spacing.



By Burndy
Catalog # [YCA2C2N](#)

Cu Compression terminal, 2 Holes, #2 (7) AWG STR, 1/2 IN Stud, 1.75 IN Spacing, 163 Index.

General

Catalog Number	YCA2C2N
Connector Type	Terminal
Die Index	163
Material	Copper
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810349915
UPC 14 Digit GTIN	00781810349915

Dimensions

Dimension - B Length fraction	1-15/79 in
Dimension - B Length inch	1.19 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.83 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	0.99 in
Dimension - Strip Length inch	1 1/4

Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Pallet Quantity	8700

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..029071-01](#)
[Specifications - YCA2C2N Specification Sheet French](#)
[Specifications - YCA2C2N Specification Sheet English](#)