



# YCA391A2N, Compression terminal for AL, ACSR, 6201, 5005, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy  
Catalog # YCA391A2N



Compression Terminals for Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors, 795 (37) 750 (61) Al, 10-1/8 in L.

## Application

For AAC(STR,Compressed,compact), ACSR AND AAAC

## General

Catalog Number	YCA391A2N
Connector Type	Terminal
Die Index	342
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Trade Name	HYLUG™
Type	YCA-R-N
UPC	781810810392
UPC 12 Digit	7818108103922

## Dimensions

Dimension - B Length inch	5.24 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.06 in
Dimension - Pad Width inch	2.32 in

## Conductor Related

Conductor - AL Str Size	750 kcmil;795 kcmil
Conductor - AL Str Size Range	750 kcmil;795 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Pallet Quantity	900

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YCA\\_LineArt](#)  
[Sales Drawings - SD..029515-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YCA391A2N-SPEC-EN | REV 6/2024