



YCA451A4N, Al compression terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 113 ACSR, 1272 kcmil AL

By Burndy
Catalog # [YCA451A4N](#)



Aluminum Terminal, 4 Pad Holes, 1113 (54-19) kcmil ACSR, 1272 (61) kcmil AL., 422 Index

General

Catalog Number	YCA451A4N
Connector Type	Terminal
Die Index	422
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016725
UPC 12 Digit	7818100167255

Dimensions

Dimension - B Length inch	4.92 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.19 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	1113 (54-19) kcmil
Conductor - ACSR Str Size Range	1113 (54/19) kcmil
Conductor - AL Str Size	1272 (61) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	8
Pallet Quantity	720

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCA_LineArt](#)
[Sales Drawings - SD..029515-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YCA451A4N-SPEC-EN | REV 6/2024