



**YCB321R, Aluminum Stirrup
Connector, 336.4-350 kcmil
Aluminum, ACSR: 300(26/7) kcmil,
336 (26/7, 26/7) 336.4 (18/1)**

By Burndy
Catalog # [YCB321R](#)



Stirrup Connector,Aluminum:336.4 kcmil-350 kcmil,
ACSR:300(26/7) kcmil, 336.4(18/1) kcmil.

General

Catalog Number	YCB321R
Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810153017
UPC 14 Digit GTIN	00781810153017

Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - Height mm	136.5 mm
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336.4 kcmil;350 kcmil
Conductor - AL Str Size Range	336.4 kcmil - 350 Kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCBR_Lineart](#)
- [Sales Drawings - 2979](#)
- [Specifications - YCB321R Specification Sheet English](#)
- [Specifications - YCB321R Specification Sheet French](#)