

YCS27A, Aluminum Sleeve

By Burndy
Catalog # [YCS27A](#)



Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop.
ANSI C119.4 CLASS 1A(PARTIAL TENSION).

General

Catalog Number	YCS27A
Connector Type	Splice
Die Index	247
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810100424
UPC 14 Digit GTIN	00781810100424

Dimensions

Dimension - B Length inch	1.94 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	0.77 in

Conductor Related

Conductor - AL Str Size	3/0 (7, 19) AWG
Conductor - AL Str Size Range	3/0 (7, 19) AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	9800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD020810-01](#)
- [Specifications - YCS27A Specification Sheet English](#)
- [Specifications - YCS27A Specification Sheet French](#)