



YCT2828, 1-piece Tap Connector

By Burndy
Catalog # [YCT2828](#)

One-piece, copper compressions tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper, Die index:168.



General

Catalog Number	YCT2828
Connector Type	Splice
Die Index	168
Die Index Run Side	168
Die Index Tap Side	168
Material	Copper
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
UPC	781810014349

Dimensions

Dimension - B Length fraction	81/89 in
Dimension - B Length inch	0.91 in
Dimension - Height fraction	4
Dimension - Height inch	4.00 in
Dimension - L Length Overall mm	145 mm
Dimension - Length BB inch	1.62 in
Dimension - Length Overall inch	5.72 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Width fraction	1-1/5 in
Dimension - Width inch	1.2 in
Dimension - Width mm	30 mm

Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Pallet Quantity	1800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCT2828_LineArt](#)
[Sales Drawings - 2208](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YCT2828-SPEC-EN | REV 6/2024