



YDS26RL, Aluminum Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS26RL](#)



AL Overhead Compression Splice - Single Sleeve Full Tension,
Accommodates: AAC, ACSR and AAC, 13-1/2 IN L.

Application

For ACSR, Aluminum, 6201 And 5005 Conductors

General

Catalog Number	YDS26RL
Connector Type	Splice
Die Index	659
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YDS-RL
UPC	781810820728
UPC 12 Digit	7818108207288

Dimensions

Dimension - B Length fraction	6-7/10 in
Dimension - B Length inch	6.7 in
Dimension - L Length Overall mm	343 mm
Dimension - Length Overall inch	13.52 in
Dimension - Outside Diameter inch	0.83 in

Conductor Related

Conductor - AAAC 5005 Size	155.4 (7) kcmil
Conductor - AAAC 5005 Size Range	155.4 (7) kcmil
Conductor - AAAC 6201 Size	155.4 (7) kcmil
Conductor - AAAC 6201 Size Range	155.4 (7) kcmil
Conductor - ACSR Cmpt Size	3/0 AWG
Conductor - ACSR Cmpt Size Range	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YDS-RL_LineArt](#)
[Sales Drawings - sd034930-01](#)



