



YDS291R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS291R](#)



2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor: 266.8 (18-1).

General

Catalog Number	YDS291R
Connector Type	Splice
Die Index	251
Die Index - Element A	240
Die Index - Element B	251
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015612
UPC 12 Digit	7818100156122

Dimensions

Dimension - Aluminum Sleeve Length inch	19.75 in
Dimension - B Length fraction	6-17/21 in
Dimension - B Length inch	6.81 in
Dimension - L Length Overall mm	502 mm
Dimension - Length Overall inch	19.75 in
Dimension - Steel Sleeve Length inch	4.125 in

Conductor Related

Conductor - ACSR Cmpt Size	4/O AWG
Conductor - ACSR Cmpt Size Range	4/O AWG
Conductor - ACSR Str Size	4/O (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/O (6/1) Penquin AWG
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YDS-R_LineArt](#)
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YDS291R-SPEC-EN | REV 6/2024