



Compression Terminal

By Burndy
Catalog # [YE26LH88](#)

Oil and water-tight terminal with shrouded, tin-plated, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer,8 IN L.



Application

Wire Termination

General

Catalog Number	YE26LH88
Connector Type	INLINE PIN
Die Index	241
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023372
UPC 12 Digit	7818100233722

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.48 in
Dimension - Inside Diameter inch	0.73 in
Dimension - L Length Overall mm	289 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.38 in
Dimension - P inch	8.06 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Compact Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	4200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YE27LH94_LineArt](#)
[Sales Drawings - SA055640-01](#)



A proud member of the Hubbell Family.