

# Compression Terminal

By Burndy  
Catalog # YE28LH128

Oil and water-tight terminal with shrouded, tin-plated, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer, 11.63 IN L.



## Application

Wire Termination

## General

Catalog Number	YE28LH128
Connector Type	INLINE PIN
Die Index	BG
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYSEALPLUG
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023396
UPC 12 Digit	7818100233966

## Dimensions

Dimension - B Length fraction	2-15/16 in
Dimension - B Length inch	2.92 in
Dimension - Inside Diameter inch	1.24 in
Dimension - L Length Overall mm	292 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.50 in
Dimension - P inch	8.06 in

## Electrical Ratings

Voltage - Maximum 35000

## Conductor Related

Conductor - Copper Str Compact Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Pallet Quantity	3150

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YE27LH94\\_LineArt](#)  
[Sales Drawings - SA055640-01](#)