

Compression Terminal

By Burndy
Catalog # YE2CLH129

Oil and water-tight terminal with shrouded, tin plated, CU barrel and brazed plug for terminating insulated CU conductor at cutout or transformer, Conductor: 2 STR.



Application

Wire Termination

General

Catalog Number	YE2CLH129
Connector Type	INLINE PIN
Die Index	162
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYSEALPLUG
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023358
UPC 12 Digit	7818100233588

Dimensions

Dimension - B Length fraction	2-3/8 in
Dimension - B Length inch	2.38 in
Dimension - Inside Diameter inch	0.91 in
Dimension - L Length Overall mm	229 mm
Dimension - Length BB inch	0.75 in
Dimension - Length Overall inch	9.00 in
Dimension - P inch	6.06 in

Electrical Ratings

Voltage - Maximum 35000

Conductor Related

Conductor - Copper Str Compact Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	4200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YE27LH94_LineArt](#)
[Sales Drawings - SA055640-01](#)