



YF1018UI, Bare Ferrule For 10 AWG

By Burndy
Catalog # [YF1018UI](#)



Cu Alloy Bare Ferrule, Smooth Funnel Entry, 10 AWG, 0.71" L,
Seamless bbl, Tin Plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

Conductor Size	10 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size

General

Catalog Number	YF1018UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479612
UPC 14 Digit GTIN	00781810479612

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Dimensions

Dimension - D inch	0.15 in
Dimension - D1 inch	0.14 in
Dimension - D2 inch	0.21 in
Dimension - Length Side A inch	0.71 in
Length	0.709 in
Width	0.205 in

Logistics

Carton Quantity	250
-----------------	-----

Conductor Related

Conductor - Copper Solid Size	10 AWG
Conductor - Copper Str Size	10 AWG

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YF_LineArt](#)
- [Sales Drawings - 10098190](#)
- [Specifications - YF1018UI Specification Sheet English](#)
- [Specifications - YF1018UI Specification Sheet French](#)
- [Specifications - BURNDY_YF1018UI_Specsheet](#)



A Hubbell brand