



YF1407UI, Bare Ferrule For 14 AWG

By Burndy
Catalog # [YF1407UI](#)



Cu Alloy Bare Ferrule, Smooth Funnel Entry, 14 AWG, 0.28" L,
Seamless bbl, Tin Plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YF1407UI
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	781810479483
UPC 14 Digit GTIN	00781810479483

Dimensions

Dimension - D inch	0.10 in
Dimension - D1 inch	0.09 in
Dimension - D2 inch	0.15 in
Dimension - Length Side A inch	0.28 in
Length	0.276 in
Width	0.15 in

Conductor Related

Conductor - Copper Solid Size	14 AWG
Conductor - Copper Str Size	14 AWG

Conductor Size	14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YF_LineArt](#)
- [Sales Drawings - 10098190](#)
- [Specifications - YF1407UI](#)
- [Specifications - BURNDY_YF1407UI_Specsheet](#)
- [Specifications - YF1407UI Specification Sheet English](#)