
YF4/032UIL - Old Version, Bare Ferrule For 4/0 AWG



By Burndy
Catalog # YF4/032UIL

Bare Ferrule For 4/0 AWG

Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Connector Type	End Termination

Dimensions

Dimension - Length Overall inch	1.26 in
Dimension - D inch	0.69 in
Dimension - D1 inch	0.66 in
Dimension - D2 inch	0.80 in

General

Sub Brand	FERRULES
Plated	Y
Insulation	N
Type	Bootlace Ferrule
Material	Copper
Plating Type	Tin - Electro Plated
UPC	621945621671

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	11600

Product Assets

Catalog [English]

© 2025 Hubbell Incorporated. All rights reserved