



YFTW1212D, Covered Twin Ferrule For 12 AWG

By Burndy
Catalog # [YFTW1212D](#)



Elect Cu Twin Insul Wire Ferrules, Smooth Funnel Entry, 12 AWG,
0.92" L, Tin Plated, Gray, For use on Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YFTW1212D
Connector Type	End Termination
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	BARE FERRULES
Type	Bootlace Ferrule
UPC	781810482155
UPC 14 Digit GTIN	00781810482155

Dimensions

Dimension - D inch	0.17 in
Dimension - D1 inch	0.15 in
Dimension - D2 inch	0.36 in
Dimension - Length Side A inch	0.92 in
Dimension - Length Side B inch	0.46 in

Conductor Related

Conductor - Copper Solid Size	12 AWG
Conductor - Copper Str Size	12 AWG
Conductor Size	12 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YFTW_LineArt](#)
- [Sales Drawings - 10099178](#)
- [Specifications - BURNDY_YFTW1212D_Specsheet](#)
- [Specifications - YFTW1212D Specification Sheet English](#)
- [Specifications - YFTW1212D Specification Sheet French](#)