



YGA262N Compression Grounding Lug, 2/0 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YGA262N](#)



HYGROUND® Grounding Irreversible Compression Terminals: 2-Hole with Inspection Window; Accommodates: 2/0 AWG; 1/2" Stud; 1-3/4" Spacing

Features

- Irreversible Compression Grounding Lug
- Inspection port to ensure proper cable insertion
- UL 467 Listed, acceptable for direct burial in earth or concrete
- Prefilled with PENETROX Oxide Inhibiting Compound and strip sealed
- 2 Stud Holes, 1/2" with 1-3/4" Spacing
- Die Index: 13

Application

For Grounding Applications And Direct Burial In Earth Or Concrete

General

Catalog Number	YGA262N
Color Code	Black
Connector Type	Terminal
Die Index	13
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220313
UPC 14 Digit GTIN	00781810220313

Dimensions

Dimension - B Length fraction	1-4/9 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	126 mm

Dimension - Length Overall inch	4.97 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	1/2 in
Dimension - Width inch	0.53 in

Conductor Related

Conductor - Copper Str Size	2/0 Str.
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	9600

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YGA2N_LineArt

Sales Drawings - SD..082469-01
Specifications - YGA262N Specification Sheet English
Specifications - YGA262N Specification Sheet French



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_CA-YGA262N-SPEC-EN | REV 4/2025