



YGA6CTC14 Compression Grounding Lug, #6 AWG Cu, 1- Hole, 1/4" Stud

By Burndy
Catalog # YGA6CTC14



Copper Compression Lug, 1 Hole w/o Inspection Probe Hole, 6 AWG, 1/4" Stud, Long Barrel.

Application

For Direct Burial In Earth Or Concrete, Grounding Applications

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810102466
UPC 12 Digit	7818101024666

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.02 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	6
Conductor - Copper Solid Size Range	6
Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Str Size Range	6 Sol / 6 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 467 • Direct Burial
Standards - Industry Standards Met	UL467;UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGA6CTC14_LineArt](#)
[Sales Drawings - SD209500](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YGA6CTC14-SPEC-EN | REV 6/2024

