



YGA8CTC14 Compression Grounding Lug, #8 AWG Cu, 1- Hole, 1/4" Stud

By Burndy
Catalog # YGA8CTC14



Grounding Irreversible Compression Terminals.

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810102442
UPC 12 Digit	7818101024422

Dimensions

Dimension - B Length fraction	4/5 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor - Copper Str Size	8 Sol./8 Str.
Conductor - Copper Str Size Range	8 Sol / 8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• UL 486A-486B
Standards - Industry Standards Met	UL467;UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGA6CTC14_LineArt](#)
[Sales Drawings - SD209500](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YGA8CTC14-SPEC-EN | REV 6/2024