



# YGHP29C29 Figure 6 Compression Grounding Connector, 1/0 Str-250 kcmil, 1/2"-5/8" Rod, 3/8"-1/2" Rebar Run, 3/0 Str-250 kcmil Tap

By Burndy  
Catalog # YGHP29C29



Cu Compression Ground Rod Connector, 3/0 Str - 250 Kcmil, 1/2" - 5/8" Rod Dia.

## Application

For Direct Burial In Earth And Concrete

## General

Connector Type	Tap
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810220948
UPC 12 Digit	7818102209488

## Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

## Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0 AWG-250 kcmil
Conductor - Rebar Run	3 ;4
Conductor - Rebar Run Range	3 -4
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Pallet Quantity	9800

## Product Assets

- [3D Models - YGHP29C29\\_MODEL-STEP](#)
- [3D Models - YGHP29C29\\_MODEL-PDF](#)
- [3D Models - YGHP29C29\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_YGHPC\\_Lineart](#)
- [Sales Drawings - sd082473-01](#)
- [Sell Sheets - HYTAP™ Figure 6 Connector, HYGROUND® Mechanical Grounding](#)



A proud member of the Hubbell Family.