

YGHR29C58TN Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR29C58TN](#)



High Strength Irreversible Compression Ground Rod Tap Connectors.

General

Connector Type	Tap
Die Index	998;1012
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAIL™
Type	Taps
UPC	781810176054
UPC 12 Digit	7818101760544

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	2-7/50 in
Dimension - Height inch	2.14 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	4/0 AWG - 250 kcmil
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Pallet Quantity	3480

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd..088266-01](#)