



YGLR34C34TN Compression Ground Rod Connector

By Burndy
Catalog # [YGLR34C34TN](#)



Tin plated Copper Compression Connector, Ground Rod to Grid, 250 kcmil - 500 kcmil, 3/4" Ground Rod or #5- #6 Rebar.

General

| | |
|--|----------------------|
| Connector Type | Tap |
| Die Index | 1011 |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | GRIDLOK™ |
| Type | Taps |
| UPC | 781810128473 |
| UPC 12 Digit | 7818101284733 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 3/4 in |
| Dimension - B Length inch | 0.75 in |
| Dimension - D inch | 0.50 in |
| Dimension - Ground Rod Size | 3/4 |
| Dimension - L Length Overall mm | 67 mm |
| Dimension - Length BB inch | 0.88 in |
| Dimension - Length Overall inch | 2.63 in |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - Copper Str Size A | 250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil |
| Conductor - Copper Str Size A Range | 250 kcmil-500 kcmil |
| Conductor - Rebar Tap | 5;6 |
| Conductor - Rod Size B | 3/4 in |
| Conductor - Rod Size B Range | 3/4 in |
| Conductor Type | <ul style="list-style-type: none">• CU C Str-Size• Rod-Size• CU Weld C Str-Size |

Certifications And Compliance

| | |
|---|----------------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | Direct Burial |
| Standards - Industry Standards Met | UL467;IEEE 837 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 6 |
| Pallet Quantity | 1440 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.