



YGS29 Compression Grounding Splice, 250 kcmil Cu

By Burndy
Catalog # YGS29



Grounding IrreversibleCompression Splices.

General

Catalog Number	YGS29
Connector Type	Splice
Die Index	16
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220436
UPC 12 Digit	7818102204366

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - Outside Diameter inch	0.75 in

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B;UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	9600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section E1 - Compression Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGS_LineArt](#)
[Sales Drawings - SD..082514-01](#)



A proud member of the Hubbell Family.