



# YHD250J1444, Stirrup

By Burndy  
Catalog # [YHD250J1444](#)



HYCRIMP™ STIRRUP.

## General

Catalog Number	YHD250J1444
Connector Type	H-Tap
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Type	Bail
UPC	781810081150
UPC 12 Digit	7818100811500

## Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.0 in
Dimension - Pad Width inch	5.00 in

## Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Size Range	4/0 AWG-300 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	16
Minimum Pack Quantity	1
Pallet Quantity	1440

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YHO100J1444\\_LineArt](#)  
[Sales Drawings - SC207318-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YHD250J1444-SPEC-EN | REV 6/2024