



YHSA10K14, Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K14](#)



Heat Shrink Ring Terminal For 12 - 10 AWG.

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

General

| | |
|--------------------------------------|------------------|
| Catalog Number | YHSA10K14 |
| Connector Type | Ring Terminal |
| EU RoHS Indicator | Yes |
| Insulation | Y |
| Insulation Type | Heat shrink |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | HYDENT |
| Trade Name | HYDENT™ |
| Type | YHS, Heat Shrink |
| UPC | 781810477021 |
| UPC 14 Digit GTIN | 00781810477021 |

Dimensions

| | |
|--------------------------------|---------|
| Dimension - B Length fraction | 2/9 in |
| Dimension - B Length inch | 0.22 in |
| Dimension - Bolt Size fraction | 1/4 |
| Dimension - Hole Size fraction | 1/4 |
| Dimension - Hole Size inch | 0.26 in |
| Dimension - Hole Size mm | 7.00 mm |

| | |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 37 mm |
| Dimension - Length Overall inch | 1.15 in |
| Dimension - N inch | 0.15 in |
| Dimension - Pad Width inch | 0.56 in |
| Dimension - Strip Length inch | 5/16 in |
| Dimension - Stud Size inch | 1/4 in |

Conductor Related

| | |
|-----------------------------------|-----------------|
| Conductor - Copper Str Size Range | 12 AWG - 10 AWG |
| Conductor Size | 12 - 10 AWG |
| Conductor Type | CU C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 100 |
| Packaging Type | Bag |

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K6_LineArt](#)
[Sales Drawings - 50094158](#)
[Specifications - YHSA10K14 Specification Sheet French](#)
[Specifications - YHSA10K14 Specification Sheet English](#)