



YHSFQ18F25X03, Fully Insulated Heat Shrink Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [YHSFQ18F25X03](#)

Fully Insulated Heat Shrink Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application


For Use On Copper Conductor

General

Catalog Number	YHSFQ18F25X03
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS
UPC	781810477144
UPC 14 Digit GTIN	00781810477144

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.28 in



Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	5/16

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSFQ18F25X03_LineArt](#)
[Sales Drawings - 50094215](#)
[Specifications - YHSFQ18F25X03 Specification Sheet English](#)
[Specifications - YHSFQ18F25X03 Specification Sheet French](#)