



Heat Shrink Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [YHSQ10M25X03](#)



Cu Heat Shrink Male Quick Disconnect, 10-12 AWG, 1.46" L, 0.25" W, Nylon Insul, Serrated bbl, Tin plated, Yellow(Insul Color).

Application

For Use On Copper Conductor

General

Catalog Number	YHSQ10M25X03
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS
UPC	781810477137

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.19 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/16

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Packaging Type	Bag
Pallet Quantity	99999

Product Assets

[3D Models - YHSQ10M25X03_MODEL-IGES](#)
[3D Models - YHSQ10M25X03_MODEL-PDF](#)
[3D Models - YHSQ10M25X03_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YHSQ18M25X03_LineArt](#)
[Sales Drawings - 50094213](#)



A proud member of the Hubbell Family.