



# Heat Shrink Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy  
Catalog # [YHSQ14M25X03](#)

Cu Heat Shrink Male Quick Disconnect, 14-16 AWG, 1.46" L, 0.25" W, Nylon Insul, Serrated bbl, Tin plated, Blue(Insul Color).



## Application

For Use On Copper Conductor

## General

|                   |                       |
|-------------------|-----------------------|
| Catalog Number    | YHSQ14M25X03          |
| Connector Type    | Male Quick Disconnect |
| EU RoHS Indicator | Yes                   |
| Insulation        | Y                     |
| Insulation Type   | Heat Shrink           |
| Material          | Copper                |
| Plated            | Y                     |
| Plating Type      | Tin                   |
| Sub Brand         | HYDENT                |
| Trade Name        | HYDENT™               |
| Type              | YHS                   |
| UPC               | 781810477113          |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length fraction   | 2/9 in  |
| Dimension - B Length inch       | 0.22 in |
| Dimension - L Length Overall mm | 32 mm   |
| Dimension - Length Overall inch | 1.25 in |
| Dimension - Pad Width inch      | 0.25 in |
| Dimension - Strip Length inch   | 5/16    |

## Conductor Related

|                                     |                                                                                       |
|-------------------------------------|---------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size       | 16 AWG;15 AWG;14 AWG                                                                  |
| Conductor - Copper Solid Size Range | 16 AWG-14 AWG                                                                         |
| Conductor - Copper Str Size         | 16 AWG;14 AWG                                                                         |
| Conductor - Copper Str Size Range   | 16 AWG - 14 AWG                                                                       |
| Conductor Size                      | 16 - 14 AWG                                                                           |
| Conductor Type                      | <ul style="list-style-type: none"><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul> |

## Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                 |       |
|-----------------|-------|
| Carton Quantity | 1200  |
| Packaging Type  | Bag   |
| Pallet Quantity | 99999 |

## Product Assets

[3D Models - YHSQ14M25X03\\_MODEL-PDF](#)  
[3D Models - YHSQ14M25X03\\_MODEL-STEP](#)  
[3D Models - YHSQ14M25X03\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Product Cross Section Image\(s\) - BUR\\_YHSQ18M25X03\\_LineArt](#)  
[Sales Drawings - 50094213](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YHSQ14M25X03-SPEC-EN | REV 6/2024